INSTRUCTION MANUAL

JUICER - MODEL ES4EA-160001-W3

-PLEASE read these instructions carefully before operating this appliance.

IMPORTANT

- -This unit is designed to operate on alternative current (A.C.) only.
- -DO NOT CONNECT TO DIRECT CURRENT (D.C.)
- -Do not leave unit in operation without an attendant.
- -When not in use for long period unplug the appliance.

INSTALLATION AND OPERATION

- -Check if voltage of your power system corresponds to the same specified on the appliance label.
- -Assembly the Unit Top(Bowl) on the Juicer.
- -Place the desired juicer implement on the drive shaft (the large implement for orange and the small for lemon).
- -Put the strainer in the juicer cup and position near the outlet of the unit top drain to catch the juice.
- -Turn on the appliance switch and place the fruit (orange or lemon cut in half) on the spinning implement and carefully press down.
- -To turn off the appliance turn off the switch.

CLEANING PROCEDURE

- -Immediately after having been used, to avoid change of juice taste, wash with water the juicer cups, strainer, implement and Unit Top (Bowl).
- -Unplug Juicer and clean body and base, using only a damp cloth.
- -Never use water jet or immerse appliance in water.
- -Wipe off appliance with a dry cloth.

he pictures/drawings are illustrations. All data can be changed without notification.







ES4EA-160001-W3



3705 NW, 115th Ave Unit 8 Doral, FL 33178 PH: +1-786-5369960

email: info@americapartstools.com






JUICER (ES4EA)




JUICER (ES4EA)



Code	Description
37.101-3	Lid
	Orange Implement
	Lemon Implement
4.064-3	Unit Top Protector
4.060-3	Unit Top (bowl)
4.006-3	Shaft
576	Screw
4.007-3	Motor Protection
4.204-3	Electric Motor
4.057-3	Body
262	Switch
643	Washer (3/16")
Under Consult	Nut
4.010-3	Bottom Cover Plate
4.306-3	Big Foot
2.082-3	Cord Connection (110V)
4.405-3	Strainer
4.406-3	Cup
4.067-3	Switch Protection
	Screw Ground
9.413-3	Cord Retainer
	Foot
2.085-3	Wiring Connector
	37.101-3 4.029-3 4.028-3 4.064-3 4.060-3 4.006-3 576 4.007-3 4.204-3 4.057-3 262 643 Under Consult 4.010-3 4.306-3 2.082-3 4.405-3 4.406-3 4.067-3

Wiring diagram



Technical Data

ES4EA-160001-W3	
Voltage (V)	120 (60Hz)
Power (HP)	1/2
Amperage (A)	4.8
Speed (rpm)	1700
Capacity (I/h)	50
Weight (kg/lbs)	7.6/16.7
Dimensions W x H x D (cm/in)	25/9.9 x 39/15.4 x 22/8.7